

Passion®



AL0043



AL0044

Description

Passion®, AL0043 and AL0044 SPECTACLES W/AROUND GREEN OR CLEAR.

Engineered to provide unparalleled eye protection in harsh environments. Boasting an ergonomic design and round green frames, they offer anti-splash protection to shield against liquid splashes, anti-dust functionality to keep debris at bay, and anti-UV protection to safeguard against harmful ultraviolet rays.

The spectacles are suitable for a wide range of wood working, carpentry, metal and construction work, lab and dental work, shooting, cycling, or anywhere need to wear PPE eyewear and outdoor applications, ensuring clarity and comfort for the wearer.

Special Instructions

- * Failure to adhere to all instructions and precautionary measures can result in injury.
- * If the user has eye conditions or vision impairment, they must consult with a registered physician prior to use.
- * Any damages to this protective device, may reduce clarity of sight that could result in injury.
- * Following any major detectable defects on the spectacle, the spectacle should be replaced immediately.
- * This spectacle is suitable for use to the lowest marking on the lens (ocular) and frame.
- * If the lens becomes damaged the spectacle should be replaced.

Although the manufacturer has examined this eyewear under the system for ensuring quality of production by means of monitoring and inspection, it is recommend that all eyewear should be thoroughly inspected before use to ensure no damage is present.

Specifications

Style: Polycarbonate with side shields
 Lens: Clear Polycarbonate
 Frame: Polycarbonate
 Mass: 35g.
 Additional: Available also in green (AL0044), clear (AL0043)

Packaging, Storage & Obsolescence

Packed as 12 individually wrapped spectacles in a box and 25 boxes per carton (300 spectacles per carton). Store in a cool dry place.



carton

Inspection Frequency and Details

Prior to use the spectacles should be free of any potential contaminants that can affect its intended performance.

The spectacles should be inspected by the user at the end of every use and again prior to each use. Cracked eyewear must be removed from service as they will reduce eye protection and obstruct vision.

Cleaning & Maintenance

Designed as re-usable protective eyewear. After use clean with a mild cleaning liquid, carefully rinse off all traces of the cleaning liquid and dry with a soft cloth and gently wipe with a soft spectacle cleaning material. Do not clean on clothing nor use abrasive cleaners.


Shelf Life

The duration of these spectacles cannot be determined by a timeline as they are intended for normal day to day use. Ensure that proper care and maintenance (inspection and cleaning) is adhered too. Under normal circumstances the spectacle should offer adequate protection for 3 years.

Disposal

All industrial waste should be disposed of correctly according to local regulations and good disposal practice. Safety eyewear should be disposed of considering the hazardous substances they were used for or could be contaminated with. Please consider recycling.

Product details



The quality is light without oppression

The use of PC materials made of protective glasses, lightweight and more comfortable material, long time to wear will not be tired.

Strong impact Resistance

PC lenses can effectively prevent iron filings, ash sand, gravel and other objects due to splash and the danger of bad eye.

129 INDUSTRIAL ROAD AMALGAM JOHANNESBURG SOUTH AFRICA

P.O.BOX 1432 CROWN MINES 2025

www.usafety.co.za